



Specification Information

Product Code: 621-P

Product Name: Disposable High-Density Polyethylene Liners for Feminine Hygiene Receptacles

Individual Carton UPC: 624622621018

Individual Carton Shipping Dimensions: 33.02cm W x 7.62cm H x 30.48cm D (13" W x 3" H x 12" D)

Individual Carton Shipping Weight: 2.3kg (5.0 lbs)

Site Location: Frost 621-P Disposable High-Density Polyethylene Liner is durable, hygienic, and environmentally friendly. These high-density poly liners are compatible across Frost's line of feminine hygiene disposals, including codes: 620, 622, 625, 633-2, 640, and 641. Typically, these units are used in schools, malls, hospitals, office buildings, recreational facilities, and other commercial properties. The simplicity and wide range of usage across Frost's feminine disposal line makes this a popular choice.



Features:

- HDPE Liner fits across family of feminine hygiene disposals (620, 622, 625, 633-2, 640, & 641)
- HDPE Liner sends 50% less material waste to landfills than traditional wax paper bags
- Natural transparent colour protects janitorial staff from unexpected discarded and dangerous items such as sharps and needles
- Secure fitting liner better contains waste from unsightly mess and exposure to bloodborne pathogens
- French/English/Spanish labeling on carton imprint
- 500 bags come per case

Capacity:

- Case includes 500 bags
- Each bag has a capacity of 8.7 litres (2.3 US gal., 1.9 Imp gal.)

Materials:

- 12 micron (approximately 0.5 mil) HDPE- natural transparent colour and unscented

Product Dimensions:

- Each bag is 25.4cm W x 30.48cm H x 10.16cm D (10" W x 12" H x 4" D) in the open position

Installation Guidelines: Frost HDPE liners can be easily inserted into any Frost feminine hygiene disposal by placing the liner inside of the respective receptacle and securing the liner over the lip of the unit. The code: 621-P can be placed directly into codes: 620 and 622 and secured over lip of the lid. Codes: 625, 6332-, 640, and 641 include internal liners to protect against spillage. The liner bags should be periodically monitored for fullness based on the frequency of use at each site.

Frost Products Ltd
5276 John Lucas Drive
Burlington, ON, Canada, L7L5Z9

(905) 332-5700
1-800 667-5094

info@frostproductsltd.com
www.Frostproductsltd.com



Handy Washroom Direct
www.handywashroom.com



Specification Information

Maintenance: Normal preventative maintenance and cleaning will keep Frost products functioning properly and may extend normal product life. Products should be wiped down with a damp soft cloth periodically. Approved stainless steel cleaner may be used to clean scuffs or fingerprints on stainless surfaces. Do not use harsh detergents or chemical cleaners. For general dirt and blemishes on painted steel or plastic use warm water and mild soap, or a general mild cleaning solution. When using any type of cleaning solution, spray onto a discrete area to test before full usage. After the cleaning agent is applied, wipe off with a clean soft cloth or sponge.

Warranty: If any product or part proves to be defective within 12 months from date of shipment from the factory it will be repaired or replaced without any charge including freight costs when authorized. Costs resulting from the installation or removal of defective products are not covered under this warranty. Discolouration to stainless steel parts resulting from exposure to harsh environmental and / or chemicals are not considered to be defects in workmanship or material and are not covered under warranty.

